

SPONSOR: **Frasch**  
Grand Prairie, TX

**Sound Absorption**  
**RAL™-A26-325**

CONDUCTED: 2026-06-16

Page 1 of 8

ON: Skinny Baffle (10") in eight rows of two objects each, rows spaced 18" on center, objects in each row spaced 1" apart

### TEST METHODOLOGY

Riverbank Acoustical Laboratories™ is accredited by the U.S. Department of Commerce, National Institute of Standards and Technology (NIST) under the National Voluntary Laboratory Accreditation Program (NVLAP) as an ISO 17025:2017 Laboratory (NVLAP Lab Code: 100227-0) and for this test procedure. The test reported in this document conformed explicitly with ASTM C423-23: "Standard Test Method for Sound Absorption and Sound Absorption Coefficients by the Reverberation Room Method." The specimen mounting was performed according to ASTM E795-23: "Standard Practices for Mounting Test Specimens During Sound Absorption Tests." A description of the measurement procedure and room specifications are available upon request. The results presented in this report apply to the sample as received from the test sponsor.

### INFORMATION PROVIDED BY SPONSOR

The test specimen was designated by the sponsor as Skinny Baffle (10") in eight rows of two objects each, rows spaced 18" on center, objects in each row spaced 1" apart. The following nominal product information was provided by the sponsor prior to testing. The accuracy of such sponsor-provided information can affect the validity of the test results.

#### **Product Under Test**

Product Name: Skinny Baffle (10")  
Manufacturer: Frasch

### SPECIMEN MEASUREMENTS & TEST CONDITIONS

Through a full external visual inspection performed on the test specimen, Riverbank personnel verified the following information:

#### **Test Specimen**

Product Type: Baffles  
Dimensions: 16 baffles @ 254 mm (10 in.) by 1200 mm (47.25 in.)  
Thickness: 9.23 mm (0.3635 in.)  
Overall Weight: 12.36 kg (27.25 lbs)

**Frasch**  
2026-06-16**RAL™-A26-325**  
Page 2 of 8**SPECIMEN MEASUREMENTS & TEST CONDITIONS (continued)****Physical Measurements (per object)**

Dimensions: 0.25 m (10.0 in) wide by 1.2 m (47.25 in) long

Thickness: 0.01 m (0.3635 in)

Weight: 0.77 kg (1.7 lbs)

**Test Environment**Room Volume: 291.98 m<sup>3</sup>

Temperature: 24.0 °C ± 0.1 °C (Requirement: ≥ 10 °C and ≤ 5 °C change)

Relative Humidity: 59.9 % ± 1.8 % (Requirement: ≥ 40 % and ≤ 5 % change)

Barometric Pressure: 97.6 kPa (Requirement not defined)

Each sound absorbing object had an exposed surface area of 0.64 m<sup>2</sup> (6.85 ft<sup>2</sup>). The total exposed surface area of all sound-absorbing objects was 10.2 m<sup>2</sup> (110 ft<sup>2</sup>).

**MOUNTING METHOD**

Type JV-MOD Mounting: The specimen is an array of 16 spaced sound absorbing objects suspended from cables such that the closest face is located approximately 1143 mm (45 in.) from the horizontal test surface. This approximates the mounting method of a typical ceiling baffle installation. The objects were distributed in eight rows of two objects each, with rows spaced 457 mm (18 in.) on center, and objects in each row spaced 25 mm (1 in.) apart. The width of the installed object array was 3251 mm (128 in.) and the length of the installed object array was 2426 mm (95.5 in.). The area of extended continuous surface attributed to the object array was 9.07 m<sup>2</sup> (97.6 ft<sup>2</sup>).

## Test Report

**Frasch**  
2026-06-16

**RAL™-A26-325**  
Page 3 of 8



Figure 1 – Specimen mounted in test chamber




Figure 2 – Detail of specimen materials

**Frasch**  
2026-06-16**RAL™-A26-325**  
Page 4 of 8**TEST RESULTS**

The preferred presentation of sound absorption test results for arrays of spaced objects is sound absorption ( $\text{m}^2$ ) per object and total sound absorption ( $\text{m}^2$ ) at each one-third-octave band

ASTM C423-23 Appendix X2 allows calculation of sound absorption per  $\text{m}^2$  ( $\text{SA}/\text{m}^2$ ) based on the projected horizontal surface area attributable to an array of objects. The extended continuous surface area used in this calculation is to be determined using the following procedure:

$S_{\text{array}} = (w + w_1) \times (l + l_1)$  If the set of objects consists of a rectangular array of equal sized objects with equal space between each object in a row and equal space between rows. (ASTM E423-23 X.2.3.1)

Where:

$S_{\text{array}}$  = area of extended continuous surface attributed to the test specimen,  $\text{m}^2$

$w$  = the measured width of the installed object array, in meters

$w_1$  = the space between objects in the array along the width, in meters

$l$  = the measured length of the installed object array, in meters

$l_1$  = the space between objects in the array along the length, in meters

The sound absorption per  $\text{m}^2$  ( $\text{SA}/\text{m}^2$ ) is calculated based on the following formula:

$$\alpha_{\text{array}} = (A_2 - A_1)/S_{\text{array}}$$

Where:

$\alpha_{\text{array}}$  = sound absorption per  $\text{m}^2$  ( $\text{SA}/\text{m}^2$ ) of extended continuous surface, no units,

$A_1$  = absorption of the empty reverberation room,  $\text{m}^2$  and

$A_2$  = absorption of the room after the specimen has been installed,  $\text{m}^2$ .

$S_{\text{array}}$  = area of extended continuous surface attributed to the test specimen,  $\text{m}^2$

**Frasch**  
2026-06-16

**RAL™-A26-325**  
Page 5 of 8

### TEST RESULTS (continued)

| 1/3 Octave<br>Center Frequency<br>(Hz) | Total Absorption  |          | Absorption per Object     |                   | $\alpha_{array}$<br>(Sabins/ft <sup>2</sup> )<br>(SA/m <sup>2</sup> ) |
|----------------------------------------|-------------------|----------|---------------------------|-------------------|-----------------------------------------------------------------------|
|                                        | (m <sup>2</sup> ) | (Sabins) | (m <sup>2</sup> / Object) | (Sabins / Object) |                                                                       |
| 100                                    | 0.57              | 6.16     | 0.04                      | 0.39              | 0.06                                                                  |
| ** 125                                 | 0.50              | 5.36     | 0.03                      | 0.33              | 0.05                                                                  |
| 160                                    | 0.75              | 8.04     | 0.05                      | 0.50              | 0.08                                                                  |
| 200                                    | 1.31              | 14.13    | 0.08                      | 0.88              | 0.14                                                                  |
| ** 250                                 | 1.59              | 17.08    | 0.10                      | 1.07              | 0.17                                                                  |
| 315                                    | 2.39              | 25.68    | 0.15                      | 1.60              | 0.26                                                                  |
| 400                                    | 2.54              | 27.35    | 0.16                      | 1.71              | 0.28                                                                  |
| ** 500                                 | 2.81              | 30.27    | 0.18                      | 1.89              | 0.31                                                                  |
| 630                                    | 3.26              | 35.13    | 0.20                      | 2.20              | 0.36                                                                  |
| 800                                    | 3.77              | 40.61    | 0.24                      | 2.54              | 0.42                                                                  |
| ** 1000                                | 4.40              | 47.41    | 0.28                      | 2.96              | 0.49                                                                  |
| 1250                                   | 5.18              | 55.77    | 0.32                      | 3.49              | 0.57                                                                  |
| 1600                                   | 5.99              | 64.50    | 0.37                      | 4.03              | 0.66                                                                  |
| ** 2000                                | 6.68              | 71.94    | 0.42                      | 4.50              | 0.74                                                                  |
| 2500                                   | 7.29              | 78.47    | 0.46                      | 4.90              | 0.80                                                                  |
| 3150                                   | 7.39              | 79.55    | 0.46                      | 4.97              | 0.82                                                                  |
| ** 4000                                | 7.54              | 81.18    | 0.47                      | 5.07              | 0.83                                                                  |
| 5000                                   | 7.76              | 83.53    | 0.49                      | 5.22              | 0.86                                                                  |


**Array-NRC 0.45** over 9.07 m<sup>2</sup> of extended continuous surface area

**Array-SAA 0.43** over 9.07 m<sup>2</sup> of extended continuous surface area

Digitally signed  
by Eric P Wolfram  
Date: 2026.07.14  
10:47:21 -05'00'

Tested by   
Marc Sciaky  
Senior Experimentalist

Report by   
Keith Kimberling  
Test Engineer

Approved by   
Eric P. Wolfram  
Laboratory Manager

*Note: Sound absorption per m<sup>2</sup> (SA/m<sup>2</sup>), and therefore the reported Single Number Ratings, are highly dependent on the exact sample shape, size, spacing, and extended continuous surface area present in the test and subsequent calculations. Changes to any of these parameters will change the resulting values. These presented results are valid only for the specific configuration present in this test.*



NVLAP LAB CODE 100227-0

**®RIVERBANK ACOUSTICAL LABORATORIES IS ACCREDITED BY NVLAP (LAB CODE 100227-0) FOR ACOUSTICAL TESTING SERVICES IN ACCORDANCE WITH ISO/IEC 17025:2017 AND FOR THIS PROCEDURE. THIS REPORT MUST NOT BE USED BY THE CLIENT TO CLAIM PRODUCT CERTIFICATION, APPROVAL, OR ENDORSEMENT BY RAL, NVLAP, NIST, OR ANY AGENCY OF THE U.S. GOVERNMENT.**


**THIS REPORT SHALL NOT BE MODIFIED WITHOUT THE WRITTEN APPROVAL OF RAL. THE RESULTS REPORTED APPLY ONLY TO THE SPECIFIC SAMPLE SUBMITTED FOR TESTING; RAL ASSUMES NO RESPONSIBILITY FOR THE PERFORMANCE OF ANY OTHER SAMPLE.**

Frasch  
2026-06-16

RAL™-A26-325  
Page 6 of 8

### SOUND ABSORPTION REPORT

Skinny Baffle (10") in eight rows of two objects each, rows spaced 18" on center,  
objects in each row spaced 1" apart



**Array-NRC 0.45** over 9.07 m<sup>2</sup> of extended continuous surface area

**Array-SAA 0.43** over 9.07 m<sup>2</sup> of extended continuous surface area

Frasch  
2026-06-16

**RAL™-A26-325**  
Page 7 of 8

### APPENDIX A: Extended Frequency Range Data

Specimen: Skinny Baffle (10") in eight rows of two objects each, rows spaced 18" on center, objects in each row spaced 1" apart (See Full Report)

*The following non-accredited data were obtained in accordance with ASTM C423-23, but extend beyond the defined frequency range of 100Hz to 5,000Hz. These unofficial results are representative of the RAL test environment only and intended for research & comparison purposes.*

| 1/3 Octave Band<br>Center Frequency | Total Absorption  |          | Absorption per Object     |                   | $\alpha_{array}$<br>(Sabins/ft <sup>2</sup> ) |
|-------------------------------------|-------------------|----------|---------------------------|-------------------|-----------------------------------------------|
| (Hz)                                | (m <sup>2</sup> ) | (Sabins) | (m <sup>2</sup> / Object) | (Sabins / Object) | (SA/m <sup>2</sup> )                          |
| 31.5                                | 0.20              | 2.13     | 0.01                      | 0.13              | 0.02                                          |
| 40                                  | 0.16              | 1.71     | 0.01                      | 0.11              | 0.02                                          |
| 50                                  | -0.15             | -1.57    | -0.01                     | -0.10             | -0.02                                         |
| 63                                  | -0.06             | -0.67    | 0.00                      | -0.04             | -0.01                                         |
| 80                                  | 0.13              | 1.44     | 0.01                      | 0.09              | 0.01                                          |
| 100                                 | 0.57              | 6.16     | 0.04                      | 0.39              | 0.06                                          |
| 125                                 | 0.50              | 5.36     | 0.03                      | 0.33              | 0.05                                          |
| 160                                 | 0.75              | 8.04     | 0.05                      | 0.50              | 0.08                                          |
| 200                                 | 1.31              | 14.13    | 0.08                      | 0.88              | 0.14                                          |
| 250                                 | 1.59              | 17.08    | 0.10                      | 1.07              | 0.17                                          |
| 315                                 | 2.39              | 25.68    | 0.15                      | 1.60              | 0.26                                          |
| 400                                 | 2.54              | 27.35    | 0.16                      | 1.71              | 0.28                                          |
| 500                                 | 2.81              | 30.27    | 0.18                      | 1.89              | 0.31                                          |
| 630                                 | 3.26              | 35.13    | 0.20                      | 2.20              | 0.36                                          |
| 800                                 | 3.77              | 40.61    | 0.24                      | 2.54              | 0.42                                          |
| 1000                                | 4.40              | 47.41    | 0.28                      | 2.96              | 0.49                                          |
| 1250                                | 5.18              | 55.77    | 0.32                      | 3.49              | 0.57                                          |
| 1600                                | 5.99              | 64.50    | 0.37                      | 4.03              | 0.66                                          |
| 2000                                | 6.68              | 71.94    | 0.42                      | 4.50              | 0.74                                          |
| 2500                                | 7.29              | 78.47    | 0.46                      | 4.90              | 0.80                                          |
| 3150                                | 7.39              | 79.55    | 0.46                      | 4.97              | 0.82                                          |
| 4000                                | 7.54              | 81.18    | 0.47                      | 5.07              | 0.83                                          |
| 5000                                | 7.76              | 83.53    | 0.49                      | 5.22              | 0.86                                          |
| 6300                                | 8.14              | 87.66    | 0.51                      | 5.48              | 0.90                                          |
| 8000                                | 8.37              | 90.06    | 0.52                      | 5.63              | 0.92                                          |
| 10000                               | 8.37              | 90.14    | 0.52                      | 5.63              | 0.92                                          |
| 12500                               | 8.85              | 95.22    | 0.55                      | 5.95              | 0.98                                          |

**Test Report****Frasch**  
2026-06-16**RAL™-A26-325**  
Page 8 of 8**APPENDIX B: Instruments of Traceability**

Specimen: Skinny Baffle (10") in eight rows of two objects each, rows spaced 18" on center, objects in each row spaced 1" apart (See Full Report)

| <b><u>Description</u></b>      | <b><u>Model</u></b> | <b><u>Serial Number</u></b> | <b><u>Date of Certification</u></b> | <b><u>Calibration Due</u></b> |
|--------------------------------|---------------------|-----------------------------|-------------------------------------|-------------------------------|
| System 1                       | Type 3160-A-042     | 3160-106968                 | 2025-07-21                          | 2026-07-21                    |
| Bruek & Kjaer Mic and Preamp H | Type 4943-B-001     | 2525859                     | 2025-11-18                          | 2026-11-18                    |
| Bruel & Kjaer Pistonphone      | Type 4228           | 2781248                     | 2025-07-21                          | 2026-07-21                    |
| EXTECH Hygro 639               | SD700               | A.103639                    | 2025-12-29                          | 2026-12-29                    |

**APPENDIX C: Revisions to Original Test Report**

Specimen: Skinny Baffle (10") in eight rows of two objects each, rows spaced 18" on center, objects in each row spaced 1" apart (See Full Report)

| <b><u>Date</u></b> | <b><u>Revision</u></b> |
|--------------------|------------------------|
| 2026-07-10         | Original report issued |

---

END